



**Inlet/Outlet Types and Cordsets**





NOTE: Illustrations are for reference only. Manufactured components may differ.

**Inlets**

**NEMA Non-locking**

5-15P	120V	15A	
5-20P	120V	20A	

**NEMA Locking**



L5-20P	120V	20A	
L5-30P	120V	30A	
L6-20P	230V	20A	
L6-30P	230V	30A	

**IEC 60320**



C20	120/230V	20A 16A - Europe	
-----	----------	---------------------	---

**Outlets**

**NEMA Non-locking**





5-15R	120V	10A	
5-20R	120V	15A	

**IEC 60320**

C13	120/230V	10A*	
C19	120/230V	20A 16A - Europe	

\*6A for Intelligent Power Tower applications, 8A for Power Tower PDU applications

## Cordsets & Headshells

<p><b>PMC1-0-1</b> IEC 60320/C19 to IEC 60320/C20 230V, 20A* 8' *16A - Europe</p>		
<p><b>PMC2-0-1 Cordset</b> NEMA 5-15P to IEC 60320/C19 120V, 15A 8'</p> <p>and</p> <p>IEC 60320/C20 to NEMA 5-15R 120V, 15A 8'</p>	  	  
<p><b>PTCORD-1</b> IEC 60320/C19 to NEMA L6-20P 230V, 20A Twist-lock 10'</p>		
<p><b>PTCORD-2</b> IEC 60320/C19 to CEE7 Schuko 230V, 10A 10'</p>		
<p><b>PTCORD-3</b> IEC 60320/C19 to IEC 60309 16/20A Blue 230V, 20A* Twist-lock 10' *16A - Europe</p>		
<p><b>PTCORD-4</b> IEC 60320/C19 to BS1363 230V, 13A 10'</p>		
<p><b>PT-ADP-C19</b> IEC 60320/C19 Cable mount headshell 230V, 20A* 10' *16A - Europe</p>		
<p><b>CAB-1302:</b> quantity 1 <b>PTCORDPK-1:</b> quantity 8 <b>PTCORDPK-2:</b> quantity 16 IEC 60320/C13 to IEC 60320/C14 120V, 10A or 230V, 6A 6'</p>		