




SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION
 THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC.
 THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION
 OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION
 OF SERVER TECHNOLOGY, INC IS PROHIBITED.

RoHS COMPLIANT


- NOTES:
1. DIMENSIONS ARE IN MILLIMETERS AND [] BRACKETS ARE IN INCHES.
 2. MOUNTING BRACKETS CAN BE MOUNTED IN SEVERAL DIFFERENT POSITIONS SEE FIG. A, B, C, AND D.
 3. SEE MOUNTING KIT DRAWING #406-0070-10 FOR DETAILS.
 4. MAXIMUM PANEL THICKNESS FOR BUTTON INTO KEYHOLE IS 2.3MM.
 5. DIMENSIONS ARE NOMINAL. INFORMATION SUBJECT TO CHANGE WITHOUT NOTICE.1




2 FIG. A
 MB-0005-IPT7




2 FIG. A
 MB-0005-IPT7



2 FIG. A
 MB-0005-IPT7



2 FIG. A
 MB-0005-IPT7



DETAIL A

<small>UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-1994 * REMOVE ALL BURRS AND SHARP EDGES. 2R MAX * DIMENSIONS ARE IN MILLIMETERS * TOLERANCES ARE: DECIMALS ± .3 ANGLES ± 1.0° DO NOT SCALE DRAWING</small>		<small>THIRD ANGLE PROJECTION</small> 		SERVER TECHNOLOGY, INC. 1040 Sandhill Drive Reno, NV 89521	
MATERIAL: FINISH: VENDOR PART NO:		APPROVALS M. RAMSEY M.RAYBURN J.MASKALY M.RAYBURN	DATE 10/27/08 10/27/08 10/27/08 10/27/08	DRAWING TITLE: OUTLINE DRAWING, CDU CX/CW-24V4 MODELS, w/ MOUNTING BRACKET OPTIONS	
		SIZE D	CAGE CODE 04V90	DWG NO. 412-0375-29	REV 1
		SCALE NONE	FILE NO. 412-0375-29.idw	SHEET 2	OF 1