




SERVER TECHNOLOGY, INC.
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

| REVISIONS | | | |
|-----------|------------------------|----------|----------|
| REV | DESCRIPTION | DATE | DFT/APPR |
| A | RELEASED TO PRODUCTION | 04/03/08 | MAR/JA |

- NOTES:
- DIMENSIONS ARE IN MILLIMETERS AND [] BRACKETS ARE IN INCHES.
 - HIDDEN BRACKETS SHOWN ARE DIFFERENT OPTIONS FOR MOUNTING.
 - SEE MOUNTING KIT DRAWING #406-0070-7 FOR DETAILS.
 - MAXIMUM PANEL THICKNESS FOR BUTTON INTO KEYHOLE PANEL IS 2.3MM.
 - DIMENSIONS ARE NOMINAL INFORMATION SUBJECT TO CHANGE WITHOUT NOTICE.



UNLESS OTHERWISE SPECIFIED
 * INTERPRET DRAWING IAW ASME Y14.100-2000
 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-1994
 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX
 * DIMENSIONS ARE IN MILLIMETERS
 * TOLERANCES ARE: DECIMALS ±.3 ANGLES ±1.0°
 DO NOT SCALE DRAWING

MATERIAL:

FINISH:

VENDOR PART NO:

THIRD ANGLE PROJECTION

| APPROVALS | DATE |
|------------|----------|
| M. RAMSEY | 03/15/06 |
| M.RAYBURN | 04/03/08 |
| J. MASKALY | 04/03/08 |
| J. ANDRADE | 04/03/08 |

SERVER TECHNOLOGY, INC.

1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
**OUTLINE DRAWING, CDU
 C-24VD2[E]-xxx MODELS, WITH
 MOUNTING BRACKET OPTIONS**

| | | | |
|------------|---------------------------|---------------------|--------|
| SIZE: D | CAGE CODE: 04V90 | DWG NO.: 412-0394-1 | REV: A |
| SCALE: 1/2 | FILE NO: 412-0394-1-3.dwg | SHEET: 3 OF 3 | |

RoHS COMPLIANT