



SERVER TECHNOLOGY, INC.
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.


| REVISIONS | | | |
|-----------|------------------------|----------|----------|
| REV | DESCRIPTION | DATE | DFT/APPR |
| A | RELEASED TO PRODUCTION | 07/25/08 | MAR/JAA |

NOTES:


1. DIMENSIONS ARE IN MILLIMETERS AND [] BRACKETS ARE IN INCHES.
2. MOUNTING BRACKETS CAN BE MOUNTED IN SEVERAL DIFFERENT POSITIONS SEE FIG. A, B, C, AND D.
3. SEE MOUNTING KIT DRAWING #406-0070-10 FOR DETAILS.
4. MAXIMUM PANEL THICKNESS FOR BUTTON INTO KEYHOLE PANEL IS 2.3MM.
5. DIMENSIONS ARE NOMINAL. INFORMATION SUBJECT TO CHANGE WITHOUT NOTICE.




2 FIG. A
 MB-0005-IPT7




2 FIG. B
 MB-0005-IPT7



2 FIG. C
 MB-0005-IPT7




2 FIG. D
 MB-0005-IPT7



RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
 * INTERPRET DRAWING IAW ASME Y14.100-2000
 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-1994
 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX
 * DIMENSIONS ARE IN MILLIMETERS
 * TOLERANCES ARE: DECIMALS ±.3 ANGLES ±1.0°
 DO NOT SCALE DRAWING



| | | |
|-----------------|----------------------------|----------|
| MATERIAL: | APPROVALS | DATE |
| FINISH: | DRAWN BY: M. RAMSEY | 05/04/06 |
| VENDOR PART NO: | CHECKED BY: M.RAYBURN | 07/25/08 |
| | APPROVED BY: J.MASKALY | 07/25/08 |
| | RELEASED BY: J. ANDRADE | 07/25/08 |

SERVER TECHNOLOGY, INC.
 1040 Sandhill Drive Reno, NV 89521

| | | | |
|--|------------------------------|-----------------------|----------|
| DRAWING TITLE: OUTLINE DRAWING, CDU, C-12V1-L[C]xxx MODELS WITH MOUNTING BRACKET OPTINS | | | |
| SIZE D | CAGE CODE 04V90 | DWG NO. 412-0387-1 | REV A |
| SCALE: 1/3 | FILE NO: 412-0387-1-2.dwg | SHEET 2 OF 3 | |