

8

7

6

5

4

3

2

1

SERVER TECHNOLOGY, INC
PROPRIETARY INFORMATION



RoHS COMPLIANT

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.


REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	A	INITIAL DESIGN	02/14/08	JM

NOTES:


1. DIMENSIONS ARE IN MILLIMETERS AND [] BRACKETS ARE IN INCHES.
2. MOUNTING BRACKETS CAN BE MOUNTED IN SEVERAL DIFFERENT POSITIONS SEE FIG. A, B, C, AND D.
3. SEE MOUNTING KIT DRAWING #406-0070-10 FOR DETAILS.
4. MAXIMUM PANEL THICKNESS FOR BUTTON INTO KEYHOLE PANEL IS 2.3MM.




2 FIG. A MB-0005-IPT7




2 FIG. B MB-0005-IPT7



2 FIG. C MB-0005-IPT7



2 FIG. D MB-0005-IPT7



<small>UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-1994 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX * DIMENSIONS ARE IN MILLIMETERS * TOLERANCES ARE: DECIMALS .3 ANGLES .1.0- DO NOT SCALE DRAWING</small>		<small>THIRD ANGLE PROJECTION</small> 		SERVER TECHNOLOGY, INC. 1040 Sandhill Drive Reno, NV 89521	
MATERIAL: SEE SEPARATE BOM		APPROVALS G.G. 02/08/08		DRAWING TITLE: OUTLINE DRAWING, SWITCHED CDU CW/CX-16Vx-xxxM MODELS WITH MOUNTING BRACKET OPTIONS	
FINISH: SEE SEPARATE BOM		CHECKED BY: M.RAYBURN 02/14/08		SIZE CAGE CODE DWG NO. REV B 04V90 412-0113-4 A	
VENDOR PART NO:		APPROVED BY: J.MASKALY 02/14/08		SCALE: 1/3.5 FILE NO: 412-0113-4.idw SHEET 2 OF 3	
RELEASED BY: J.ANDRADE 02/14/08		DATE 02/14/08			

8

7

6

5

4

3

2

1