






SERVER TECHNOLOGY, INC  
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.





REVISIONS			
REV	DESCRIPTION	DATE	DFT/APPR
A	RELEASED TO PRODUCTION	07/25/08	MAR/JAA

- NOTES:
- DIMENSIONS ARE IN MILLIMETERS AND [ ] BRACKETS ARE IN INCHES.
  - MOUNTING BRACKETS CAN BE MOUNTED IN SEVERAL DIFFERENT POSITIONS SEE FIG. A, B, C, AND D.
  - SEE MOUNTING KIT DRAWING #406-0070-10 FOR DETAILS.
  - MAXIMUM PANEL THICKNESS FOR BUTTON INTO KEYHOLE PANEL IS 2.3MM.
  - DIMENSIONS ARE NOMINAL. INFORMATION SUBJECT TO CHANGE WITHOUT NOTICE.




2 FIG. A  
 MB-0005-IPT7

2 FIG. B  
 MB-0005-IPT7



2 FIG. C  
 MB-0005-IPT7

2 FIG. D  
 MB-0005-IPT7



UNLESS OTHERWISE SPECIFIED  
 \* INTERPRET DRAWING IAW ASME Y14.100-2000  
 \* DIMENSIONING & TOLERANCING IAW ASME Y14.5M-1994  
 \* REMOVE ALL BURRS AND SHARP EDGES .2 R MAX  
 \* DIMENSIONS ARE IN MILLIMETERS  
 \* TOLERANCES ARE: DECIMALS ±.3 ANGLES ±1.0°  
 DO NOT SCALE DRAWING

MATERIAL:

FINISH:

VENDOR PART NO:

THIRD ANGLE PROJECTION	
APPROVALS	DATE
DRAWN BY: M. RAMSEY	04/20/06
CHECKED BY: M.RAYBURN	07/25/08
APPROVED BY: J.MASKALY	07/25/08
RELEASED BY: J. ANDRADE	07/25/08

SERVER TECHNOLOGY, INC.

1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:  
**OUTLINE DRAWING, CDU  
 C-24V1-Lxxx[C20] MODELS  
 WITH MOUNTING BRACKET OPTIONS**

SIZE D	CAGE CODE 04V90	DWG NO. 412-0388-1	REV A
SCALE: 1/3	FILE NO: 412-0388-1-2.dwg	SHEET 2 OF 3	

RoHS COMPLIANT