



**During your evaluation of this Server Technology Sentry CDU(s), the following are a few key features to consider:**

**CW-Series: Switched Product Line**

- Easy to use and access, secure, integral HTML Web GUI over HTTP/S, plus LDAP/S and TACACS+ external authentication and authorization support
- Secure remote power management; reboot individual or grouped outlets (SSL, SSH, Telnet, SNMP, RS-232)
- Outlets maybe linked to one or multiple groups without loss of control of that individual outlet
- Native power-up sequencing prevents in-rush current overload during initial start-up or after power loss. Unlike other products on the market, sequencing occurs during initial startup, after power loss and after user-initiated power cycling to prevent overload.
- True RMS input current monitor(s) on easy-to-read local LED, via network or serial connection
- Optional temperature and humidity probes with 10-ft cords to allow sensors to be located in different locations
- SNMP traps provide automated alerts for power and environmental conditions. Additionally, event notification is available via Syslog and email.
- Expandability: add additional outlets under one IP address through link unit (STI Model CX CDUs)
- Remote Shutdown Agent: initiate shutdown of remote servers, protecting open application files prior to server being powered down.
- Smart Load Shedding option: initiates shut down based on high temperature, high input feed load and UPS 'On Battery' conditions.
- Local and remote notification if a branch circuit is down (FE will display on LED and through the web-based interface, SNMP and email alerts)
- 3-phase products have a separate LED for each phase to simplify load balancing.
- Branch Circuit Protection – meetings UL 60950-1
- Available in 120/208/230V, 16A/20/30/32A, single-phase and 3-phase