Sentry 48DCWB-04-4X070-DONB

Key Features

Remote Power Management:
 Combine intelligent power
 distribution and remote power
 control into a single 2U 19"
 rack-mount enclosure

- > Input Power Feeds: Four (4) 100-amp inputs to support dual power supply servers and networking gear
- > Outlets: One (1) high-amp (to 70A) individually fused outlet per input power feed
- > IP Access & Security: Web interface, SSL, SSH, Telnet, SNMP, FTP, SNTP, Syslog, LDAP(S), TACACS+, RADIUS, and RS-232 access
- Expansion: Add an expansion PDU (48DCXB) to a master PDU (48DCWB) for additional monitoring and management under the same IP address
- > Environmental Sensors: Add two
 (2) probes on 10ft leads that each measure temperature and humidity

Intelligent -48 VDC Power Distribution, Remote Management, Power & Environmental Monitoring



48DCWB-04-4X070-DONB

The Sentry 48DCWB-04-4X070-DONB Intelligent PDU and Remote Power Manager minimizes the impact of locked-up routers, servers and other network devices on business-critical networks. CLECs, ILECs, ISPs and enterprises use the Sentry 48DCWB-04-4X070-DONB to manage equipment in remote sites, co-location facilities and network operation centers. Sentry 48DCWB-04-4X070-DONB eliminates the need to dispatch a field service technician for manual intervention when devices lock-up. Using a Sentry 48DCWB-04-4X070-DONB, the network operations center can quickly restart locked-up remote network servers to ensure that the network is fully operational around the clock.

Sentry 48 VDC provides immediate operational cost savings, including:

> Reduced field service visits > Improved problem/solution response time

> Improved network availability > Improved facility security

Eliminate the Need for a Separate Power Distribution Panel

The Sentry 48DCWB is an intelligent unit that combines the functions of a power distribution panel and remote power management unit into a 2.5U 19" rack-mounted enclosure. Each power output terminal connection is rated to switch 70 amps and is protected by interchangeable TPC fuses allowing for the current rating to be adjusted onsite.

Measurement Features

Use RS-232 and/or TCP/IP to monitor the status of key measurement values. Receive SNMP or email alerts as well as Syslog when a measurement value is out of a predefined threshold:

> Input Feed/Outlet "On Sense" - Verifies power at each power input/outlet connection

> Load Sense - Provides an accurate, real time measurement of the current draw, in amps, for each power outlet

> Environmental Sensors - Supports two external probes that each measure temperature and humidity

Model Number and Technical Specifications

Model

48DCWB-04-4X070-DONB (Master) 48DCXB-04-4X070-DONB (Expansion)

Power Input

> Four (4) 70A power input terminal blocks (+/- & G), -48 VDC nominal (-40 VDC to -60 VDC)

Power Output

> Four (4) 70 amp outputs (1 per power input) > Each outlet individually protected by a TPC fuse (sold separately) > Available TPC fuses: 10, 15, 20, 25, 30, 40, 50, 60, and 75 amp

Communications and Security

- > 10/100 BaseT Ethernet
- > HTTP/HTTPS
- > SSLv3/TLSv1
- > SNMPv2c & v3
- > SSHv2
- > Telnet
- > LDAPS/LDAPv3
- > TACACS+
- > RADIUS
- > RS-232 (Serial)
- Dimensions
- > 2.5U, 432 x 112 x 407 mm [17.0 x 4.4 x 16.0 in.]

Agency Approvals

- > NEBS Level 3
- > GR-1089-Core: Sections 1-4, 7, 9, and 10
- > GR-63-Core: Sections 4.1, 4.2, 4.3, 4.4, 4.5, and 4.7
- > ESTI: 300 019-2-1, -2, and -3
- > ESTI: EN 300 132-2 V2.2.2: 2007-10

> US & Canada (cTUVus Mark) to UL 60950-1:2007 and

- CAN/CSA 22.2 No. 60950-1-07
- > EU (TUVGS Mark) to EN 60950-1:2006 +A11
- > FCC Class A, Part 15
- > CE Mark

Accessories

Optional Accessories

- > EMTH-1-1 Combination Temperature/Humidity Probe, 10ft (3m)
- > EMCU-1-1B Environmental Monitor adding
 - Two (2) EMTH-1-1 Temperature/Humidity Probes (one included)
 - One (1) EMWS-1-1 Water Sensor (sold separately)
 - Four (4) Dry Contact (NO/NC) monitoring points
 - One (1) 8-bit analog-to-digital converter (0 to 5VDC)
- > SPM (Sentry Power Manager)
 - Monitor and manage multiple PDUs from a single point
 - Monitor and manage alarm conditions
 - Create reports and trends on stored data
 - Control and analyze power usage per power supply and device
 - Optional appliance or virtual version
 - VMware READY

Warranty

> 2 years



VMware and VMware Ready is a registered trademark or trademark of VMware, Inc. in the United States and/or other jurisdictions

Expansion Module Model Number > 48DCXB-04-4X070-DONB





HEADQUARTERS - NORTH AMERICA Server Technology, Inc. 1040 Sandhill Drive Reno, NV 89521 United States 1.775.284.2000 Tel 1.775.284.2065 Fax sales@servertech.com www.servertech.com www.servertechblog.com

Western Europe, Middle East and Africa Server Technology Fountain Court 2 Victoria Square Victoria Street St. Albans AL1 3TF United Kingdom +44 (0) 1727 884676 Tel

+44 (0) 1727 220815 Fax salesint@servertech.com

Central Europe, Eastern Europe and Russia Niederlassung Deutschland Server Technology LLC 42119 Wuppertal Germany Tel: + 49 202 693917 x 0 Fax: + 49 202 693917-10 salesint@servertech.com

APAC Server Technology Room 2301, 23/F, Future Plaza 111-113 How Ming Street, Kwun Tong, Hong Kong Direct line: +852 3916 2048 Fax Line: +852 3916 2002 salesint@servertech.com