


Server Technology®

A brand of  legrand®



Product Catalog

1-800-835-1515
sales@servertech.com
www.servertech.com



stay powered.



be supported.



get ahead.

TABLE OF CONTENTS

About Legrand®	3
About Server Technology®	4
Why Server Technology?	5
Advanced Technologies	6
HDOT® Cx	7
Per Outlet Power Sensing (POPS®)	8
Per Inlet Power Sensing (PIPS®)	9
PDU Families	10-11
PDU Features	12-13
Switched POPS® PDUs	14-15
Switched PDUs	16-17
Smart POPS® PDUs	18-19
Smart PDUs	20-21
Metered PDUs	22-23
Basic PDUs	24-25
-48VDC PDUs	26-27
Power Cords and Accessories	28
Build Your Own PDU	29-32
Rack PDU Selector	33-34
Discover, Research, Buy	35

ABOUT LEGRAND®

Legrand is the global specialist in electrical and digital building infrastructures. Its comprehensive offering of solutions for use in commercial, industrial, and residential markets makes it a benchmark for customers worldwide. Drawing on an approach that involves all teams and stakeholders, Legrand is pursuing its strategy of profitable and sustainable growth driven by acquisitions and innovation, with a steady flow of new offerings—including connected products stemming from Legrand’s global Eliot (Electricity and IoT) program.




Legrand is one of the most sustainable companies in the world, as ranked by the Corporate Knights, and is committed to achieving carbon, water, and waste reductions in its operations, deepening its community relationships, and continuously improving the environmental profile of its products. Legrand reported sales of around \$7.1 billion (USD) in 2017. Legrand has a strong presence in North and Central America, with a portfolio of well-known market brands and product lines. Legrand is listed on Euronext Paris and is a component stock of indexes including the CAC40, www.legrand.us

In November 2017, Server Technology became part of the Data Power and Control Division of Legrand North and Central America (LNCA). Legrand’s Data Power and Control Division, which also includes; Raritan, Universal Electric, StarLine, Electrorack, and Ortronics, is committed to innovation and leadership in the complex data center marketplace. Server Technology’s robust offering of intelligent PDU product lines strengthens LNCA’s ability to deliver on this commitment.

Global Vision

We transform the spaces where people live and work, through innovative products and solutions that deliver and manage power, light, and data.

We do this by relentlessly pursuing both sustainable business practices and the creation of exceptional experiences through the products we design and manufacture, the relationships we build and the way we work.



ABOUT SERVER TECHNOLOGY®

Server Technology, a brand of Legrand, is leading the engineering and manufacturing of customer-driven, innovative and exceptionally reliable power, access and control solutions for monitoring and managing critical IT assets for continual availability.

Server Technology's power strategy experts are trusted to provide Rack PDU solutions for data centers worldwide ranging from small technology startups to Fortune 100 powerhouses. Because power is all we do, Server Technology can be found in the best cloud and colocation providers, forward thinking labs, and telecommunications operations.



Server Technology customers consistently rank us as providing the highest quality PDUs, the best customer support, and most valuable innovation. We have over 12,000 PDU configurations to fit every data center need and most of our PDUs are shipped within 10 days.

Mission Statement

Through engineering talent, imagination and a commitment to quality, we design, develop and provide the world's best power management products and systems.

Customer Commitment

At Server Technology, we pride ourselves in going the extra mile for customers. Whether it's our expert customer support staff talking you through technical needs or our vast library of product documentation, our goal is to help you Stay Powered, Be Supported and Get Ahead.

WHY SERVER TECHNOLOGY?



Stay Powered

Focused Only on Power

All we do is PDU's and Power Management

Testing of Every PDU and Outlet

Guarantees Product Reliability and Accuracy

Highest Quality PDUs

Assembled in the USA



Be Supported

Superior Support

#1 Differentiator Compared to Our Competitors

PDUs to Meet any Demand

Largest PDU Selection on the Market

PDUs Ship in 10 Days

Get Your PDU when you need it



Get Ahead

Customer Driven Information

Most Patents in Industry

Cutting Edge Power Solutions

*Only Multi-Award Winning PDU on the Market; HDOT | HDOT Cx

Future Ready PDUs

Build Your Own PDU in 4 Steps: BYOPDU

*2018 - **Data Centre PDU Product of the Year** - High Density Outlet Technology (HDOT) with Alternating Phase Outlets Rack PDU in Switched and Smart POPS

*2016 - **Data Centre PDU Product of the Year** - HDOT Rack Mount PDU in Switched and Smart POPS

*2014 - **Data Center Dynamics North America Innovator Finalist** - HDOT

ADVANCED TECHNOLOGIES

Our suite of advanced technologies in Per Outlet Power Sensing (POPS®), Switched, Smart, and Metered PDUs were developed to satisfy specific data center requirements.

HDOT®

Server Technology PDUs with High Density Outlet Technology (HDOT) has the highest outlet count in smallest form factor and are the most popular on the market. Available in POPS, Switched, and Smart PDUs solve today's top data center challenges: Power Density, Capacity Planning, and Remote Power Management. Maximize outlet density with our uniquely designed, high density modules for C13 and C19 outlets.




PRO2®


Improve uptime by maintaining high availability to your data through redundantly powered hot-swappable network cards and multi-link capability. Gain additional insight into rising loads or heat through multi-level alarms. Optional combination temperature and humidity probes with 10 ft. cords offer flexibility in terms of sensor placement.

Alternating Phase Technology

Alternating phase outlets alternate the phased power on a per-outlet basis instead of a per-branch basis. This allows for shorter cords, quicker installation and easier load balancing for 3-phase rackmount PDUs. Shorter cords mean less mass, making them less likely to come unplugged during transport of the assembled rack or getting in the way when servicing the cabinet. Plus, less cables blocking air flow helps keep your equipment cool and improves efficiencies.



Traditional PDU



Alt-Phase PDU

HDOT® CX

The Highest Density Plus Ultimate Flexibility Solution

The Best PDU Just Got Better with the New HDOT Cx. Server Technology's award winning HDOT (High Density Outlet Technology) has been improved with our Cx outlet. The HDOT Cx welcomes change as data center equipment is replaced. The Cx outlet is a hybrid of the C13 and C19 outlets. HDOT Cx accommodates both C20 and C14 plugs. This innovative design reduces the complexity of the selection process while lowering end costs. With HDOT Cx, you won't have to buy a new set of PDUs when equipment changes.



Limitless Possibilities One Standard PDU

- Combines two outlets into one
- Most outlets per form factor
- Easy load balancing with alternating phase technology
- Future ready for equipment updates
- Available in Smart, Switched, and POPS
- Build Your Own PDU in 4 easy steps
- Ships in 10 business days



Server Technology's original HDOT is our most popular PDU solution. HDOT PDUs can be found in the most demanding data centers worldwide ranging from small technology startups to Fortune 100 powerhouses. With the addition of the Cx outlet, customers can now have a PDU that provides the best density in the market and the ultimate flexibility for future equipment updates. Customers rank us as providing the highest quality PDUs, the best customer support and most valuable innovation.




PER OUTLET POWER SENSING (POPS®)

The best outlet power measurement technology on the market for data center device-level power monitoring. POPS prepares Smart and Switched PDUs for environments that require high density computing. A POPS equipped PDU offers device-level output measurement capability, allowing you to track and manage servers, applications, IT equipment, and the equipment cabinet infrastructure. With the ability to measure, monitor, and report power down to the rack or outlet level, this solution follows the Green Grid's recommendations for acquiring the most accurate power monitoring data.



With a POPS equipped Smart or Switched PDU you can:

- Monitor SNMP traps, email alerts, configuration changes, system events, load, temperature, and humidity
- Group outlets across master and expansion PDUs
- Remote configuration and environmental monitoring
- Ping an IP address to see if equipment is responding
- Receive alerts for power, control state, current, and power factor
- Use open API to share device level power data with other systems in your infrastructure




PER INLET POWER SENSING (PIPS®)

The best inlet power measurement technology on the market for data center rack-level power monitoring. **PIPS** technology replaces monitoring at the remote power panel in data centers with higher accuracy and lower cost monitoring of each power circuit attached to a PDU. PIPS enhances Smart and Switched PDUs with the most accurate and complete power metrics on the market. Expect the same quality and functionality of an intelligent PDU, but with an increased level of data to help you make critical decisions regarding your facility.



With a PIPS equipped Smart or Switched PDU you can:

- Monitor current, voltage, power, apparent power, crest factor, reactance, power factor, accumulated energy, temperature and humidity
- Configure outlets, alarms, thresholds, grouping, permissions, email alerts, security settings, communication settings and SNMP traps
- Quickly confirm the status of rack power and environmental conditions
- Use open API to share device level power data with other systems in your infrastructure



PDU FAMILIES

SWITCHED POPS PDUs



Switched POPS PDUs is our most feature rich family, it includes everything from our Switched family plus combines highly accurate, outlet-level power measurement technology for data center device-level power monitoring, alerting and on/off/reboot control. With outlet control, gain features like power-up sequencing and smart load shedding. POPS combined with device-level output control, allows you to monitor, track and manage servers, IT equipment and the equipment cabinet infrastructure.

SWITCHED PDUs

Switched PDUs can turn on, off, or reboot outlets individually or as a group. Switched PDUs also feature outlet lock-out, power-up sequencing to reduce power-up inrushes and optional smart load shedding. Not only do these PDUs feature Smart PDU abilities for network access to power and environmental information, but they also give outlet control for reboot of locked-up devices as well as power-up sequencing.

SMART POPS PDUs



Smart POPS PDUs feature highly accurate, outlet-level power monitoring for your data center power needs. Email alerts provide automated updates on power and environmental conditions. Expansion PDUs may be used to provide full access to all power feeds in a cabinet under a single IP address. SNMP traps email automated alerts provide consistent insight into your outlet's power levels and surrounding conditions.

SMART PDUs

Smart PDUs are easy-to-use and access, these PDUs offer input current monitors on LED via network or serial connection. Smart PDUs feature branch circuit protection and are available in a variety of voltages and amperages. Available in both single- and three- phase.

METERED PDUs

Metered PDUs feature Auto-flip current displays to help prevent overloads and simplify three-phase load balancing in high density cabinets. Optional flexible mounting allows you to mount the PDU in standard or custom brackets. If you're looking for reliable power distribution for all the devices located in your equipment cabinet, Metered PDUs might be the perfect affordable solution.

PDU FAMILIES

BASIC PDUs

Basic PDUs are UL Listed and meet IEC data center requirements. Optional flexible mounting and color identification features are available. Basic PDUs provide reliable power distribution for all devices in your equipment cabinet. Basic PDUs are available in single-phase 110-120V or 208-240V power distribution with 20A or 30A options and 3-Phase power distribution with 20A and 30A options.

-48VDC PDUs

-48VDC PDUs provide control of cabinet equipment at remote locations, including colocation facilities and network ops centers giving you the ability to reboot locked up remote servers around the clock. Features also include individual outlet current outputs, measurements and automated alerts for a number of low and high current needs for the given environmental conditions.

Choose the Right PDU

PDU FAMILY	Branch Circuit Protection	Input Current Monitoring	Enviro Monitoring	Access, Security & Comm	Expansion Module	Individual Outlet Control	Per Outlet Power Monitoring
Switched POPS	✓	✓	✓	✓	✓	✓	✓
Smart POPS	✓	✓	✓	✓	✓		✓
Switched	✓	✓	✓	✓	✓	✓	
Smart	✓	✓	✓	✓	✓		
Metered	✓	✓					
Basic	✓						

PDU FEATURES

As a leader in product innovation, Server Technology holds many of the key patents for providing power in zero-u and horizontal PDU configurations compatible with today's rack and dense compute infrastructure requirements. Server Technology's advanced features help reduce downtime, facilitate capacity planning, improve energy efficiency and drive efficiency.



HDOT[®] Cx

The HDOT Cx outlet is a hybrid of the C13 and C19 outlets. Cx outlets accommodate C20 and C14 plugs, increasing density while providing ultimate flexibility.



HDOT[®] (High Density Outlet Technology)

Maximize outlet density with our uniquely designed, high density modules for standard C13 & C19 outlets



Alternating Phase

Phased power is alternated between each outlet, instead of each branch, which simplifies load balancing and cord clutter.



Outlet Control

Switched PDUs can cycle power to individual outlets or groups of outlets to reboot servers or power off unused receptacles.



POPS[®] (Per Outlet Power Sensing)

Monitor Current Load (A), Voltage (V), Power (W), Apparent Power (VA), Crest Factor, Power Factor and Energy per outlet.



PIPS[®] (Per Inlet Power Sensing)

Monitor Current Load (A), Voltage (V), Power (W), Apparent Power (VA), Crest Factor, Power Factor and Energy per inlet.



Input Current Monitoring

LEDs display current per phase to help prevent over-loads and simplify 3-phase load balancing in high density cabinets.



Branch Current Monitoring

Monitors current at each breaker/fuse branch and alerts when high usage risks a tripped circuit. (PRO2[®] only)



Branch Circuit Protection

PDUs are UL 60950-1 certified for branch circuit protection and use fuses or circuit breakers to protect each outlet branch.



Temperature/Humidity Monitoring

Master and Link units each support two external 10' (3m) T/H probes. Receive SNMP-based alerts and email notifications.

PDU FEATURES



Temperature/Humidity Monitoring

Master and Link units each support two external 10' (3m) T/H probes. Receive SNMP-based alerts and email notifications.



IP Access, Security & Communications

Web, SSH, Telnet, SNMPv2c & v3, RS-232 serial, 10/100 Base T-Ethernet, LDAP(S), TACACS+, RADIUS, DHCP and SMTP/email.



Star Multi-link Expansion Kit

Provides the ability to link up to four power circuits using one IP address. Kit sold separately. (PRO2® only)



Linked Expansion

Exclusive method for linking additional PDUs together under a single IP address with support for A&B power in-feeds.



High Temperature Rating

Products are tested and approved for safe and reliable operation in 60°C (140°F) data center environments.



Hot Swappable Network Card with Backup Power

Network access is ensured when power is lost to the Master unit. (PRO2® only)



Flexible Mounting

Includes standard button mounts along with provisions for custom mounting brackets (contact Server Technology for details).



Cable Retention

Reduces accidental disconnects by ensuring that power cords are solidly connected to their respective devices.



Color Coded PDUs

Select from six colors to designate PDU circuits in the data center; black, white, red, green, blue and yellow.



Startup Stick™

The quick and easy solution to CDU configuration when DHCP is not available.

SWITCHED POPS® PDU_s



Switched POPS combines outlet power measurement technology for data center device-level power monitoring, alerting and on/off/reboot control. Use the Switched functionality to cycle power on dual power IT equipment with one command. With outlet control, gain features like power-up sequencing and smart load shedding.



Blade servers and high density computing power requirements continue to increase and POPS is the right PDU for monitoring and managing those types of environments. POPS combined with device-level output control, allows you to monitor, track and manage servers, IT equipment and the equipment cabinet infrastructure.

Popular Configurations

MODEL: C2WG36TE-YQME2M66

208V 3 Phase Delta 60A



Input Power Capacity	17.3kW
Input Voltage	208V
Input Current	60A
Phase	3-Phase Wye (L-L)
Plug Type	208V Wye 60A IEC 60309 3P+N+G 9Hr
W x H x D	2.2 x 70.0 x 2.5 in. (64.0 x 1778.0 x 56.0 mm.)
Mounting	OU Vertical
Alternating Phase	Yes

MODEL: STV-6541C

208V Single Phase 30A



Input Power Capacity	5kW
Input Voltage	208V
Input Current	30A
Phase	1-Phase (L-L)
Plug Type	NEMA L6-30P
W x H x D	1.75 x 64.0 x 3.5 in. (89.0 x 1626.0 x 45.0 mm.)
Mounting	OU Vertical
Alternating Phase	No



SWITCHED POPS® PDUs

Sample Configurations

Model	Total Outlets	Input Power Capacity	Input Voltage	Input Current	Phase	Plug Type	W x H x D	Mounting	Alt Phase
STV-6541C	24	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	1.75 x 64 x 3.5 in. (89 x 1626 x 45 mm)	OU Vertical	No
STV-6501C	30	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	2.2 x 69 x 2.25 in. (56 x 1753 x 58 mm)	OU Vertical	No
C2WG36TE-2CAF2M66	36*	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	No
C2WG36TE-YCMFAM66	36*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	Yes
C2WG36TE-DCMFAM66	36*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	Yes
C2WG36TE-2QAF2M66	36*	10kW	208V	60A	1-Phase (L-L)	IEC 208V/60A 2P+G 6Hr	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	No
C2WG36TE-YQME2M00	36*	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	Yes
C2WG36TE-YQME2M66	36*	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	Yes
STV-6521D	48	17.3kW	208V	60A	3-Phase Delta (L-L)	IEC 60309 3P+G 9Hr	3.25 x 69 x 3 in. (77 x 1753 x 83 mm)	OU Vertical	No
STV-6521Y	48	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	3.25 x 69 x 3 in. (77 x 1753 x 83 mm)	OU Vertical	No
C2WG48TE-DQME2M99	48*	17.3kW	208V	60A	3-Phase Delta (L-L)	IEC 60309 3P+G 9Hr	2.2 x 80 x 2.5 in. (64 x 2032 x 56 mm)	OU Vertical	Yes
C2WG48TE-YQME2M99	48*	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	2.2 x 80 x 2.5 in. (64 x 2032 x 56 mm)	OU Vertical	Yes
STV-6503Z	30	17.3kW	415V	30A	3-Phase Wye (L-N)	NEMA L22-30P	2.2 x 70 x 2.25 in. (58 x 1778 x 56 mm)	OU Vertical	No
STV-6503D	30	17.3kW	415V	30A	3-Phase Wye (L-N)	IEC 60309 3P+N+G 6Hr	2.2 x 70 x 2.25 in. (58 x 1778 x 56 mm)	OU Vertical	No
STV-6509Z	36	17.3kW	415V	30A	3-Phase Wye (L-N)	NEMA L22-30P	2.19 x 70 x 2.25 in. (58 x 1778 x 56 mm)	OU Vertical	No
C2WG36TE-5CAF2M66	36*	17.3kW	415V	30A	3-Phase Wye (L-N)	NEMA L22-30P	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	Yes
C2WG48TE-5PAF2M99	48*	17.3kW	415V	30A	3-Phase Wye (L-N)	IEC 60309 3P+N+G 6Hr	2.2 x 80 x 2.5 in. (64 x 2032 x 56 mm)	OU Vertical	Yes
C2WG08HC-2CBA2DAC	8	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	17.2 x 1.75 x 7 in. (178 x 45 x 437 mm)	1U Horizontal	No
C2WG12SM-2CJA2D3	12*	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	17.2 x 1.75 x 11.57 in. (294 x 45 x 437 mm)	1U Horizontal	No
C2WG24SN-DCLN5D6	24*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	17.2 x 3.50 x 17.5 in. (294 x 89 x 445 mm)	2U Horizontal	Yes

*Contains HDOT Cx Outlets

Can't find the right PDU? Server Technology has you covered.



Rack PDU Selector
Over 2000 standard configurations
servertech.com/product-selector



Build Your Own PDU
Build an HDOT or HDOT Cx PDU in 4 easy steps
byopdu.servertech.com

SWITCHED PDUs



Switched PDUs can turn on, off, or reboot outlets individually or as a group. Switched PDUs also feature outlet lock-out and power-up sequencing to reduce power-up inrushes and smart load shedding. These PDUs provide Smart abilities for network access to power and environmental information. Switched PDUs also give outlet control for reboot of locked-up devices and power-up sequencing.

Switched PDUs are perfect for all environments that require power + environmental monitoring, power-up sequencing, rebooting and scheduling power loads. These Switched PDUs have been especially useful in rapidly growing environments, such as those found in colocation facilities. Switched PDUs can be purchased with HDOT Cx and Alternating Phase technology.

Popular Configurations

MODEL: C2W36TE-DQME2M99

208V 3 Phase Delta 30A



Input Power Capacity	8.6kW
Input Voltage	208V
Input Current	30A
Phase	3-Phase Delta (L-L)
Plug Type	NEMA L15-30P
W x H x D	3.25 x 69.0 x 2.25 in. (58.0 x 1753.0 x 83.0 mm.)
Mounting	OU Vertical
Alternating Phase	Yes

MODEL: STV-4523D

415V 3 Phase Wye 30A



Input Power Capacity	17.3kW
Input Voltage	415V
Input Current	30A
Phase	3-Phase Wye (L-N)
Plug Type	240/415V Wye 30A IEC 60309 3P+N+G 6Hr
W x H x D	3.25 x 69.0 x 2.25 in. (58.0 x 1753.0 x 83.0 mm.)
Mounting	OU Vertical
Alternating Phase	No

SWITCHED PDUs

Sample Configurations

Model Number	Total Outlets	Input Power Capacity	Input Voltage	Input Current	Phase	Plug Type	W x H x D	Mounting	Alt Phase
STV-4541C	24	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	69 x 1.75 x 2.25 in. (1753 x 45 x 58 mm)	OU Vertical	No
STV-4501C	30	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	69 x 2.2 x 2.3 in. (1753 x 56 x 59 mm)	OU Vertical	No
C2W36TE-2CAF2M99	36*	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	No
C1W24VS-YCFA13C9	24	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	69 x 1.75 x 2.25 in. (1753 x 45 x 58 mm)	OU Vertical	No
C2W36TE-YCMFAM99	36*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	Yes
C2W42CE-DCMFAM00	42	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	Yes
C2W48TE-DCMFAM99	48*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	2.2 x 80 x 2.5 in. (64 x 2032 x 56 mm)	OU Vertical	Yes
STV-4522E	48	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	3.25 x 69 x 2.25 in. (58 x 1753 x 83 mm)	OU Vertical	No
STV-4522M	48	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	3.25 x 69 x 2.25 in. (58 x 1753 x 83 mm)	OU Vertical	No
C2W54CE-DCMFAM00	54	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	2.2 x 80 x 2.5 in. (64 x 2032 x 56 mm)	OU Vertical	Yes
C2W36TE-2QAF2M99	36*	10kW	208V	60A	1-Phase (L-L)	IEC 208V/60A 2P+G 6Hr	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	No
C2W42CE-2QAF2M00	42	10kW	208V	60A	1-Phase (L-L)	IEC 208V/60A 2P+G 6Hr	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	No
C2W36TE-YQME2M99	36*	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	Yes
C2W48TE-YQME2M99	48*	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	2.2 x 80 x 2.5 in. (64 x 2032 x 56 mm)	OU Vertical	Yes
STV-4526D	48	17.3kW	208V	60A	3-Phase Delta (L-L)	IEC 60309 3P+G 9Hr	3.25 x 69 x 2.75 in. (70 x 1753 x 83 mm)	OU Vertical	No
C2W36TE-5CAF2M66	36*	17.3kW	415V	30A	3-Phase Wye (L-N)	NEMA L22-30P	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	Yes
C2W48TE-5CAE2M99	48*	17.3kW	415V	30A	3-Phase Wye (L-N)	NEMA L22-30P	2.2 x 80 x 2.5 in. (64 x 2032 x 56 mm)	OU Vertical	Yes
STV-4523Z	48	17.3kW	415V	30A	3-Phase Wye (L-N)	NEMA L22-30P	3.25 x 69 x 2.25 in. (58 x 1753 x 83 mm)	OU Vertical	No
C1W08HC-2CBA2BAC	8	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	1.75 x 17.2 x 7 in. (45 x 437 x 178 mm)	1U Horizontal	No
C1W16HR-2CAA5BAC	16	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	3.5 x 17.2 x 7.1 in. (89 x 437 x 181 mm)	2U Horizontal	No

*Contains HDOT Cx Outlets 

Can't find the right PDU? Server Technology has you covered.



Rack PDU Selector
Over 2000 standard configurations
servertech.com/product-selector



Build Your Own PDU
Build an HDOT or HDOT Cx PDU in 4 easy steps
byopdu.servertech.com

SMART POPS® PDUs



Smart POPS PDUs feature highly accurate, outlet-level power monitoring for your data center power needs. Email alerts provide automated updates on power and environmental conditions. Expansion PDUs may be used to provide full access to all power feeds under a single IP address. SNMP traps and email automated alerts provide consistent insight into your outlet's power levels and surrounding conditions.



With POPS, each unit provides measurements for loads, voltage, active power, apparent power, crest factor, power factor and energy power consumption. Smart POPS PDUs feature built-in LED current monitors, which feature an Ethernet, serial and temperature/humidity monitoring port, while optional temperature and humidity probes on 10 ft. cords allow for measurements to be taken in different locations within the cabinet.

Popular Configurations

MODEL: C2SG48TE-YQME2M99

208V 3 Phase Wye 60A



Input Power Capacity	17.3kW
Input Voltage	208V
Input Current	60A
Phase	3-Phase Wye (L-L)
Plug Type	208V Wye 60A IEC 60309 3P+N+G 9Hr
W x H x D	3.25 x 69.0 x 2.25 in. (58.0 x 1753.0 x 83.0 mm.)
Mounting	OU Vertical
Alternating Phase	Yes

MODEL: STV-5542E

208V 3 Phase Delta 30A



Input Power Capacity	8.6kW
Input Voltage	208V
Input Current	30A
Phase	3-Phase Delta (L-L)
Plug Type	NEMA L15-30P
W x H x D	1.75 x 69.0 x 3.5 in. (89.0 x 1753.0 x 45.0 mm.)
Mounting	OU Vertical
Alternating Phase	No



SMART POPS® PDUs

Sample Configurations

Model Number	Total Outlets	Input Power Capacity	Input Voltage	Input Current	Phase	Plug Type	W x H x D	Mounting	Alt Phase
STV-5541C	24	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	1.75 x 61 x 3.5 in. (89 x 1550 x 45 mm)	OU Vertical	No
C2SG36TE-2CAF2M66	36*	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	No
STV-5542L	24	5.7kW	208V	20A	3-Phase Wye (L-L)	NEMA L21-20P	1.75 x 69 x 3.5 in. (89 x 1753 x 45 mm)	OU Vertical	No
STV-5542D	24	5.7kW	208V	20A	3-Phase Wye (L-L)	NEMA L15-20P	1.75 x 69 x 3.5 in. (89 x 1753 x 45 mm)	OU Vertical	No
C2SG36TE-DCMFAM66	36*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	Yes
C2SG36TE-YCMFAM66	36*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	Yes
C2SG48TE-YCMFAM99	48*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	2.2 x 80 x 2.5 in. (64 x 2032 x 56 mm)	OU Vertical	Yes
C2SG36TE-2QAF2M66	36*	10kW	208V	60A	1-Phase (L-L)	IEC 208V/60A 2P+G 6Hr	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	No
C2SG36TE-YQME2M66	36*	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	Yes
C2SG48CE-YQME2M66	48*	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	2.2 x 80 x 2.5 in. (64 x 2032 x 56 mm)	OU Vertical	Yes
C2SG48TE-YQME2M99	48*	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	2.2 x 80 x 2.5 in. (64 x 2032 x 56 mm)	OU Vertical	Yes
C2SG36TE-5CAE2M66	36*	17.3kW	415V	30A	3-Phase Wye (L-N)	NEMA L22-30P	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	Yes
C2SG48TE-5CAE2M99	48*	17.3kW	415V	30A	3-Phase Wye (L-N)	NEMA L22-30P	2.2 x 80 x 2.5 in. (64 x 2032 x 56 mm)	OU Vertical	Yes

*Contains HDOT Cx Outlets 

Can't find the right PDU? Server Technology has you covered.



Rack PDU Selector
Over 2000 standard configurations
servertech.com/product-selector



Build Your Own PDU
Build an HDOT or HDOT Cx PDU in 4 easy steps
byopdu.servertech.com

SMART PDUs



Easy to use and access, Smart PDUs from Server Technology offer input current monitors on easy-to-view LED via network or serial connection. These PDUs feature branch circuit protection and are available in a variety of voltages, amperages. Available in single- and three-phase.

Smart PDUs are guaranteed secure and feature external authentication and authorization support, while SNMP traps provide automated alerts surrounding each outlet's power and environmental conditions. Optional temperature and humidity probes, with 10 ft. cords, offer flexibility in terms of sensor placement.

Popular Configurations

MODEL: C2S48TE-YQME2M99

208V 3 Phase Wye 60A



Input Power Capacity	17.3kW
Input Voltage	208V
Input Current	60A
Phase	3-Phase Wye (L-L)
Plug Type	208V Wye 60A IEC 60309 3P+N+G 9Hr
W x H x D	2.2 x 80.0 x 2.5 in. (64.0 x 2032.0 x 56.0 mm.)
Mounting	OU Vertical
Alternating Phase	Yes

MODEL: C2S54CE-DQME2M00

208V 3 Phase Delta 60A



Input Power Capacity	17.3kW
Input Voltage	208V
Input Current	60A
Phase	3-Phase Delta (L-L)
Plug Type	208V Delta 60A IEC 60309 3P+G 9Hr
W x H x D	2.2 x 80.0 x 2.5 in. (64.0 x 2032.0 x 56.0 mm.)
Mounting	OU Vertical
Alternating Phase	Yes

SMART PDUs

Sample Configurations

Model Number	Total Outlets	Input Power Capacity	Input Voltage	Input Current	Phase	Plug Type	W x H x D	Mounting	Alt Phase
STV-3531C	30	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	60 x 1.75 x 2.25 in. (1524 x 45 x 58 mm)	OU Vertical	No
C2S36TE-2CAF2M99	36*	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	No
C2S36TE-DCMFAM99	36*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	Yes
C2S36TE-YCMFAM99	36*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	Yes
C2S48TE-YCMFAM99	48*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	2.2 x 80 x 2.5 in. (64 x 2032 x 56 mm)	OU Vertical	Yes
C2S48TE-DCMFAM99	48*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	2.2 x 80 x 2.5 in. (64 x 2032 x 56 mm)	OU Vertical	Yes
C2S36TE-2QAF2M99	36*	10kW	208V	60A	1-Phase (L-L)	IEC 208V/60A 2P+G 6Hr	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	No
C2S42CE-2QAF2M00	42	10kW	208V	60A	1-Phase (L-L)	IEC 208V/60A 2P+G 6Hr	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	No
STV-3534D	30	17.3kW	415V	30A	3-Phase Wye (L-N)	IEC 60309 3P+N+G 6Hr	70.1 x 1.75 x 2.25 in. (1781 x 45 x 58 mm)	OU Vertical	No
C2S36TE-YQME2M99	36*	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	Yes
C2S42CE-YQME2M00	42	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	2.2 x 70 x 2.5 in. (64 x 1778 x 56 mm)	OU Vertical	Yes
C2S48TE-YQME2M99	48*	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	2.2 x 80 x 2.5 in. (64 x 2032 x 56 mm)	OU Vertical	Yes
C2S54CE-DQME2M00	54	17.3kW	208V	60A	3-Phase Delta (L-L)	IEC 60309 3P+G 9Hr	2.2 x 80 x 2.5 in. (64 x 2032 x 56 mm)	OU Vertical	Yes
C2S54CE-YQME2M00	54	17.3kW	208V	60A	3-Phase Wye (L-L)	IEC 60309 3P+N+G 9Hr	2.2 x 80 x 2.5 in. (64 x 2032 x 56 mm)	OU Vertical	Yes
C2S48TE-5CAE2M99	48*	17.3kW	415V	30A	3-Phase Wye (L-N)	NEMA L22-30P	2.2 x 80 x 2.5 in. (64 x 2032 x 56 mm)	OU Vertical	Yes
C2S48TE-5PAE2M99	48*	17.3kW	415V	30A	3-Phase Wye (L-N)	IEC 60309 3P+N+G 6Hr	2.2 x 80 x 2.5 in. (64 x 2032 x 56 mm)	OU Vertical	Yes
C1S10SA-2CBA2B4	10*	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	1.75 x 17.2 x 7 in. (45 x 437 x 178 mm)	1U Horizontal	No
C1S24SP-2CAA4A6	24*	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	3.5 x 17.2 x 7 in. (89 x 437 x 178 mm)	2U Horizontal	No
C2S24SP-YCLN5D6	24*	8.6kW	208V	30A	3-Phase Wye (L-L)	NEMA L21-30P	17.2 x 3.5 x 10 in. (254 x 89 x 437 mm)	2U Horizontal	Yes
C2S24SP-DCLN5D6	24*	8.6kW	208V	30A	3-Phase Delta (L-L)	NEMA L15-30P	17.2 x 3.5 x 10 in. (254 x 89 x 437 mm)	2U Horizontal	Yes

*Contains HDOT Cx Outlets 

Can't find the right PDU? Server Technology has you covered.



Rack PDU Selector
Over 2000 standard configurations
servertech.com/product-selector



Build Your Own PDU
Build an HDOT or HDOT Cx PDU in 4 easy steps
byopdu.servertech.com

METERED PDUs

Metered PDUs feature auto-flip current displays to help prevent overloads and simplify three-phase load balancing in high density cabinets, while optional flexible mounting allows you to mount the PDU in standard or custom brackets. If you're looking for reliable power distribution for all the devices located in your equipment cabinet, Metered PDUs might be the perfect affordable solution.



Metered PDUs feature local input current monitoring, which allows you to verify the aggregated load on the outlet's circuit or phase. With branch circuit protection, Metered PDUs are perfect for a range of equipment cabinets, from 2kW-22kW. Available in single-phase 110-120V or 208-240V or 3-Phase power distribution with 20A, 30A, 50A, or 60A options.

Popular Configurations

MODEL: C-12H1B211E7

120V Single Phase 30A



Input Power Capacity	2.8kW
Input Voltage	120V
Input Current	30A
Phase	1-Phase (L-N)
Plug Type	NEMA L5-30P
W x H x D	17.2 x 1.75 x 5.0 in. (127.0 x 45.0 x 437.0 mm.)
Mounting	1U Horizontal
Alternating Phase	No



MODEL: STV-2001C

208V Single Phase 30A



Input Power Capacity	5kW
Input Voltage	208V
Input Current	30A
Phase	1-Phase (L-L)
Plug Type	NEMA L6-30P
W x H x D	1.75 x 60.0 x 2.25 in. (58.0 x 1524.0 x 45.0 mm.)
Mounting	OU Vertical
Alternating Phase	No



METERED PDUs

Sample Configurations

Model Number	Total Outlets	Input Power Capacity	Input Voltage	Input Current	Phase	Plug Type	W x H x D	Mounting	Alt Phase
C-12V1-C20M	12	1.9kW	120V	20A	1-Phase (L-N)	IEC C20 Inlet	1.75 x 31.25 x 2.25 in. (58 x 794 x 45 mm)	0U Vertical	No
C-12V1-L30M	12	2.8kW	120V	30A	1-Phase (L-N)	NEMA L5-30P	1.75 x 31.25 x 2.25 in. (58 x 794 x 45 mm)	0U Vertical	No
STV-2001C	30	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	1.75 x 60 x 2.25 in. (58 x 1524 x 45 mm)	0U Vertical	No
C-12H1B211E7	12	2.8kW	120V	30A	1-Phase (L-N)	NEMA L5-30P	17.2 x 1.75 x 5 in. (127 x 45 x 437 mm)	1U Horizontal	No
C-12H0A113	12	3.3kW	208V	20A	1-Phase (L-L)	IEC C20 Inlet	17.2 x 1.75 x 5 in. (127 x 45 x 437 mm)	1U Horizontal	No
C-12H2C211	12	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	1.75 x 17.2 x 5 in. (45 x 437 x 127 mm)	1U Horizontal	No

Can't find the right PDU? Server Technology has you covered.



Rack PDU Selector
Over 2000 standard configurations
servertech.com/product-selector



Build Your Own PDU
Build an HDOT or HDOT Cx PDU in 4 easy steps
byopdu.servertech.com

BASIC PDUs



Basic PDUs from Server Technology are UL Listed and meet IEC data center requirements. Optional flexible mounting and color identification features are available. Basic PDUs provide reliable power distribution for all devices in your equipment cabinet and ranges in power from 2kW-6kW per cabinet. Basic PDUs are available in single-phase 110-120V or 208-240V power distribution with 20A or 30A options and 3-Phase power distribution with 20A and 30A options.

Popular Configurations

MODEL: CB-24V2C401-001

208V Single Phase 30A



Input Power Capacity	5kW
Input Voltage	208V
Input Current	30A
Phase	1-Phase (L-L)
Plug Type	NEMA L6-30P
H x W x D	1.75 x 34.0 x 2.0 in. (51.0 x 864.0 x 45.0 mm.)
Mounting	0U Vertical
Alternating Phase	No



MODEL: CB-12H1-L530

120V Single Phase 30A



Input Power Capacity	2.8kW
Input Voltage	120V
Input Current	30A
Phase	1-Phase (L-N)
Plug Type	NEMA L5-30P
H x W x D	17.2 x 1.75 x 2.25 in. (58.0 x 45.0 x 437.0 mm.)
Mounting	1U Horizontal
Alternating Phase	No



BASIC PDUs

Sample Configurations

Model Number	Total Outlets	Input Power Capacity	Input Voltage	Input Current	Phase	Plug Type	W x H x D	Mounting	Alt Phase
CB-24V2C401-001	24	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	1.75 x 34 x 2 in. (51 x 864 x 45 mm)	0U Vertical	No
CB-26V2CE01F6	26	5kW	208V	30A	1-Phase (L-L)	NEMA L6-30P	1.75 x 35.5 x 1.75 in. (45 x 902 x 45 mm)	0U Vertical	No
CB-12H1-C20	12	1.9kW	120V	20A	1-Phase (L-N)	IEC C20 Inlet	17 x 1.75 x 2.25 in. (58 x 45 x 432 mm)	1U Horizontal	No
CB-12H1-L530	12	2.8kW	120V	30A	1-Phase (L-N)	NEMA L5-30P	17.2 x 1.75 x 2.25 in. (58 x 45 x 437 mm)	1U Horizontal	No
CB-12H2-C20	12	3.3kW	208V	20A	1-Phase (L-L)	IEC C20 Inlet	17 x 1.75 x 2.25 in. (58 x 45 x 432 mm)	1U Horizontal	No

Can't find the right PDU? Server Technology has you covered.



Rack PDU Selector

Over 2000 standard configurations

servertech.com/product-selector

-48VDC PDUs



-48VDC PDUs provide control of cabinet equipment at remote locations, including colocation facilities and network ops centers giving you the ability to reboot locked up remote servers around the clock. Features also include individual outlet current outputs, measurements and automated alerts for a number of low and high current needs for the given environmental conditions.

-48VDC PDUs feature Fused or Breaker Power Output Protection, meaning each low and high current output is individually protected by its own over current protection device. These are available in a variety of current capacities. Low current GMT fuses have a visual indicator that show when they're blown. Because the fuses are rated as disconnect switches, they can be hot-swappable without removing power to input-feeds. Optional temperature and humidity probes with 10-ft cords to allow sensors to be located in different locations for complete environmental monitoring.

Popular Configurations

MODEL: 48DCWB-16-2X600-E0

-48VDC 600A Dual-Input

Input Power Capacity	57.6kW
Input Voltage	-48V
Input Current	1200A
Phase	DC
Input Type	Terminals
W x H x D	17.0 x 7.0 x 32.0 in. (813.0 x 178.0 x 432.0 mm.)
Mounting	4U Horizontal
Alternating Phase	No



MODEL: 48DCWB-04-2X100-DONB

-48VDC 100A Dual-Input

Input Power Capacity	9.6kW
Input Voltage	-48V
Input Current	200A
Phase	DC
Input Type	Terminals
W x H x D	17.0 x 3.5 x 16.0 in. (407.0 x 89.0 x 432.0 mm.)
Mounting	2U Horizontal
Alternating Phase	No

-48VDC PDUs**Sample Configurations**

Model Number	Total Outputs	Input Power Capacity	Input Voltage	Input Current	Input Type	W x H x D	Mounting	Alt Phase
48DCWB-04-2X100-DONB	4	9.6kW	-48V	200A	Terminals	17.0 x 3.5 x 16.0 in. (407.0 x 89.0 x 432.0 mm.)	2U Horizontal	No
48DCWB-08-2X100-BONB	8	9.6kW	-48V	200A	Terminals	17.0 x 3.5 x 16.0 in. (407.0 x 89.0 x 432.0 mm.)	2U Horizontal	No
48DCWB-04-4X125-EONB	4	24kW	-48V	500A	Terminals	17.0 x 4.4 x 16.0 in. (407.0 x 112.0 x 432.0 mm.)	2.5U Horizontal	No
48DCWB-10-2X300-EONB	10	28.8kW	-48V	600A	Terminals	17.0 x 5.25 x 20.0 in. (508.0 x 134.0 x 432.0 mm.)	3U Horizontal	No
48DCWB-16-2X600-E0	16	57.6kW	-48V	1200A	Terminals	17.0 x 7.0 x 32.0 in. (813.0 x 178.0 x 432.0 mm.)	4U Horizontal	No

Can't find the right PDU? Server Technology has you covered.



Rack PDU Selector

Over 2000 standard configurations


servertech.com/product-selector

POWER CORDS AND ACCESSORIES


20A PLUGS and CORDS						
Model	PTCORD-L1	PTCORD-L5	PTCORD-L6	PTCORD-L7	HARD-WIRED	HARD-WIRED
Outlets	L6-20P to C19	5-15P to C19	5-20P to C19	L5-20P to C19	NEMA L15-20P	NEMA L21-20P
Voltage	208-240V	100-120V	100-120V	100-120V	3-Phase 208V, Wye	3-Phase 208V, Wye
Amps	20A	15A	20A	20A	20A	20A
Length	10' 3m	10' 3m	10' 3m	10' 3m	10' 3m	10' 3m
Profile						
30A PLUGS and CORDS						
Model	HARD-WIRED	HARD-WIRED	HARD-WIRED	HARD-WIRED	HARD-WIRED	HARD-WIRED
Outlets	NEMA L5-30P	NEMA L6-30P	NEMA L15-30P	NEMA L21-30P	NEMA L22-30P	NEMA L22-30P
Voltage	100-120V	208-240V	3-Phase 208V, Delta	3-Phase 208V, Wye	3-Phase 208V, Wye	277/480V, Wye
Amps	30A	30A	30A	30A	30A	30A
Length	10' 3m	10' 3m	10' 3m	10' 3m	10' 3m	10' 3m
Profile						
50A and 60A PLUGS and CORDS						
Model	HARD-WIRED		HARD-WIRED		HARD-WIRED	
Outlets	CS8365C		IEC 60309 (4pin, 9hr)		IEC 60309 (5pin, 9hr)	
Voltage	3-Phase 208-240V, Delta		3-Phase 208-240V, Delta		3-Phase 208V, Wye	
Amps	50A		60A		60A	
Length	Varies Based on Model		Varies Based on Model		Varies Based on Model	
Profile						
Accessory Options						
Model	EMTH-2-10	EMCU-1-1C	KIT-0016	KIT-SUS-01	KIT-PRO2LINK-01D	
Desc	Temperature & Humidity Probes	Environmental Monitoring Control Unit	C20 Inlet Retention Bracket	StartUp Stick	Multi-Link Module for PRO1 and PRO2 PDUs	
Function	Measures cabinet temperature & humidity	Supports 2 additional EMTH-2-10 water & 4 dry contact closure door sensors	Securely fastens C19 cord to chassis	Easy solution to PDU configuration, start up in 5 seconds	Add up to 3 Expansion PDUs to one Master to share one IP address	
Profile						

BUILD YOUR OWN PDU

Visit byopdu.servertech.com to build an HDOT or HDOT Cx PDU in 4 steps




Choose from HDOT or HDOT Cx outlets




Select the PDU product family of your choice

BUILD YOUR OWN PDU




Choose your voltage, amperage and phase type




Select your modules and form factor

BUILD YOUR OWN PDU



Choose your plug type



Your custom PDU configuration and model number are generated

BUILD YOUR OWN PDU



Server Technology
A brand of **Avigilon**

C2S51TE-DQME2M90 (Master)
C2L51TE-DQME2M90 (Expansion)

The Server Technology® PRO2® Smart PDU provides local LED input current monitoring, allowing IT personnel to determine safe levels of loading on a per-phase basis while installing equipment into the rack/cabinet. The integral PIPS® technology provides billing-grade accurate measurement of current, voltage, active power, apparent power, power factor, crest factor, and accumulated energy at the input. These power data points, along with temperature and humidity measurements (provided via optional probes), are accessible through the built-in Web and CLI interfaces as well as through SNMP. The PRO2 Smart "Master" PDU can be connected to as many as three (with optional module) PRO2 Smart "Link" PDU to extend the network access to the redundant or secondary power feed without the risks of a daisy chain linking configuration.

Key Features

Cx Outlets

Alt Phase

Branch Circuit Protection

Branch Current Monitoring

Cisco Energy Wise®

Environmental Monitoring

Flexible Mounting

HDOT

High Retention Outlets

High Temperature

Hot Swappable

Input Current Monitor

Multi Link Expansion

Network Monitoring

PDU Colors

Per Inlet Power Sensing

Inputs

Input Voltage: 208
Input Plug: IEC 60309 3P + PE 60A IP44
Input Current: 60
Input Current Rated: 48
Cord Entry: End
Cord: 10ft (3m), 4-conductor, 6AWG

Outputs

Connector: (42) x IEC 60320/C13
North American Rating (C13): < 12A @208V L-L (15A Peak)
Connector: (9) x Cx
North American Rating (Cx): < 16A @208V L-L (20A Peak)

Outlet #1 opposite cord end

Locking outlets provide high-retention even for non-locking cords. The Cx outlet has superior cable retention. Moderate force is required when plugging in a C14 or C20 connector to fully seat the plug and to ensure proper installation. An incorrectly installed plug will be loose and will not provide a reliable connection.

Branch Circuit Protection

UL489 compliant 2-pole, 20A trip circuit breakers, six (6) branches, rating: < 16A @220-240V

Physical

Dimensions: 80in (2032mm) tall x 2.2in (56mm) wide x 2.5in (64mm) deep | **Weight:** 39lbs (18.03kg)
Highlight Color: Choose Black, White, Red, Green, Blue, Yellow

Environmental

Operating Environment: 32°F to 140°F / 0°C to 60 °C | 8%RH to 90%RH non-condensing | 6,500ft/2km elevation
Storage Environment: -40°F to 185°F / -40°C to 85°C | 8%RH to 90%RH non-condensing | 50,000ft/15km elevation
 Quiescent / Unloaded Power Draw: < 10W for all configurations

Communications & Security

10/100 Mbps Ethernet (RJ-45 connector), RS-232 serial (RJ-45 connector)
 Two (2) temperature/humidity sensor inputs (4P4C), Link port (RJ-12) - (also on Link PDU)
 Web-browser GUI and command-line interface (CLI): HTTP/HTTPS, TSLV1.2, SSHv2, Telnet, SNMPv2c and v3 (GET, SET, Traps), IPv4 and IPv6, LDAPv3/LDAP5, TACACS+, RADIUS, FTP/SFTP

Drawings

Mechanical Drawing

NOTES:
 1. DIMENSIONS ARE MILLIMETERS UNLESS OTHERWISE SPECIFIED IN INCHES.
 2. DIMENSIONS ARE GIVEN AS NOMINALS UNLESS OTHERWISE SPECIFIED AS TOLERANCES.

Additional Information

Warranty: Server Technology offers a standard 2-year limited parts & labor warranty. Extended support is available at the time of purchase. See the Support Options on the website, or contact your local Server Technology representative for more information.

Patents: Information on Server Technology patents is available on the website at:
www.servertech.com/products/patents

PRO2, HDOT, PIPS, POPS, CDU, Sentry, Server Technology, and the globe logo are U.S. registered trademarks of Server Technology, Inc. Power Pivot, EZip, and StartUp Stick are trademarks of Server Technology, Inc.

Information in this document is current as of time of publishing. Contact your Server Technology representative for the most up-to-date information. © 2018 Server Technology, Inc.

¹ Cisco EnergyWise is a U.S. registered trademark of Cisco Technology, Inc.

Interested in learning more about how Server Technology can help you manage and distribute power in your datacenter? Visit us online at: www.servertech.com/products/

<p>North America Headquarters 1000 Sandhill Road Reno, Nevada 89521 1-775-284-2000 Tel 1-800-835-1515 Toll Free 1-775-284-2045 Fax sales@servertech.com www.servertech.com www.servertechblog.com</p>	<p>U.K. Western Europe, Israel & Africa Fontenay Court 2 Victoria Square Victoria Street St. Albans AL1 3TF United Kingdom +44 (0) 1727 886676 Tel +44 (0) 1727 208118 Fax sales@servertech.com</p>	<p>Germany Central Europe, Eastern Europe & Russia 10th + 11th Floor Westhafen Tower Westhafenplatz 1 60327 Frankfurt Germany +49 69 1045 6205 Tel +49 69 1045 6450 Fax sales@servertech.com</p>	<p>Hong Kong APAC Level 43, AIA Tower 183 Electric Road, North Point, Hong Kong +852 3975 1008 Tel +852 3975 1800 Fax sales@servertech.com</p>
<p>India & Middle-East Level 9, Rajhira Towers, 28-27 Mahatma Gandhi Road Bangalore, Karnataka, 560 001, India +91 80 40927227 Tel sales@servertech.com</p>			


Server Technology
A brand of **Avigilon**

Stay Powered. Be Supported. Get Ahead.


©2018 Server Technology, Inc. Version 01/20/2018. Sentry and Server Technology are registered trademarks of Server Technology. Incorporated information is subject to change without notice. Printed in USA. Server Technology offers a wide range of products for North America and Global markets; for more information visit our website at www.servertech.com

RACK PDU SELECTOR

Browse over 2000 PDU configurations at servertech.com/product-selector



The Rack PDU Selector allows you to filter type, mounting, outlets, voltage, current, phase and plug type.



The product family page will show you all of the specifications and features for that product family.

RACK PDU SELECTOR



Have a power strategy expert contact me
PR02™ HDOT® 11.0kW - 22.0kW (36-42) outlets Rack PDU

First Name:	<input type="text"/>	Zip/Postal Code:	<input type="text"/>
Last Name:	<input type="text"/>	Country:	<input type="text" value="United States"/>
Company:	<input type="text"/>	Email:	<input type="text"/>
State/Province:	<input type="text" value="Alabama"/>	Telephone:	<input type="text"/>

An authorized representative will contact you within 24 hours.

DISCOVER, RESEARCH, BUY



Rack PDU Buying Guide

Find the best PDU for your data center
servertech.com/rack-pdu-buying-guide



Rack PDU Selector

Over 2000 standard configurations
servertech.com/product-selector



Build Your Own PDU

Build an HDOT or HDOT Cx PDU in 4 easy steps
byopdu.servertech.com



Speak to a Power Expert

Get free technical support
servertech.com/support



How to Buy

Tools to simplify the PDU buying process
servertech.com/how-to-buy



About Us

Stay Powered, Be Supported, Get Ahead
servertech.com/about-us

1-800-835-1515
sales@servertech.com
www.servertech.com

**Server
Technology**[®]
A brand of  **legrand**